



# Ultrasonic LoRaWAN Multi Thread Adaptor Kit

Tekelek P/N: 18-0429



The **Multi Thread adaptor** is equipped with an NBR seal and grub screws and is attached to the pairing adaptor which can be connected to the base of the Ultrasonic LoRaWAN sensor.



Also supplied as part of this kit are:

**Mounting Adaptor** which can be mounted onto the tank. The Multi Thread adaptor can be screwed into this mounting adaptor.



**Mounting Gasket** which is to be placed between the tank and the Mounting Adaptor.



**2 x No.8 X 13mm PAN POZI screws** which secure the Mounting Adaptor to the tank.



**Allen Key** to tighten/loosen grub screws.



**Installation Guide** which contains the procedure for implementing this kit.

